

MODEL CME 45 HANDWASHER DRIER SPECIFICATION SHEET

INSTALLATION (A)

The CME_45 unit is designed for front service access. The unit is suitable for installation into brick, timber or metal pre-fabricated wall types. To aid installation and ensure alignment within the wall, installation wall plates are provided. Fixing points are arranged on each plate (positions 'A'). The unit cabinet is secured to the wall plates with bolts (supplied).

ELECTRICAL (B)

Single Phase ac 50Hz -
 Power ratings: 220v : 2650w, 230v : 2850w, 240v : 3100w

A supply feed of 1.25mm twin & earth cable should be terminated into a 13 Amp fused double pole isolating switch which has a contact separation of at least 3mm, positioned local to the unit. The cable is fed into the unit through the rear face at position 'B'.

WASTE (C)

The unit should be fitted with a *deep seal waste trap* that will accept a pipe size of 1 1/4" Ø. Traps are available from Wallgate, P/No WW3960 (S bend) or WW3967 (P bend).

WATER (D)

A cold water supply of minimum pressure 1.75 bar is required. The supply pipe of 15mm dia., is connected to the flow regulator stop tap at position 'D' which has a 15mm compression connection. Contact Wallgate for connection to gravity fed or low pressure supplies.

SOAP

A liquid soap must be used - soap reservoir capacity: 4 ltr.
 A range of liquid soaps is available from Wallgate.

DIMENSIONS

Weight: 58kg
 Cabinet size: 940 x 540 x 255mm
 Fascia size: 1000 x 600mm +/-10
 Full installation details are supplied with each unit and can be obtained from WALLGATE®.



Refer to technical sheet CME_45s_dis.

APPROVALS

Patent No:1365763



BS476 Pt 6 Class 0 & 7 Class 1 – non inflammable rating.
 NFF 16101 – toxicity and smoke rating F0 (least density and emissions)
 BS EN 438 pt1 – highly resistant and tested for resistance to : surface wear, immersion in boiling water, dry heat, impact by a small ball, staining, UV light and cigarette burns.

